

ENDURANCE TECHNOLOGY

ROD-STYLE ELECTRIC ACTUATOR rsa-h'

The HT option is a high thrust version of the 24, 32, 50 and 64 sizes of the RSA series. RSA HT actuators offer a roller screw option to meet even the most demanding applications

WHY CHOOSE THE HT OPTION?

- Higher strength components transfer more torque from the gearhead/motor to the actuator screw
- · Grease zerk allows convenient relubrication for extended screw service life
- · Allows convenient addition of gearbox to RP (Reverse Parallel mount) actuator
- Accommodates mounting large motors with up to 165mm bolt circle pattern

YOUR MOTOR HERE

YOU CAN CHOOSE:

Specify motor to be installed and actuator ships with proper mounting hardware

REDESIGNED LMI & RP HOUSING

Specially designed to accommodate larger motors & gearboxes with higher torques and larger bolt circles (up to 6.5", 165mm)

DURABLE BELT MATERIAL

High torque polyurethane timing belt with carbon tensile cords resists stretching

GREASE ZERK

Standard feature allows easy re-lubrication



ENHANCED HIGH THRUST BEARING

High thrust angular contact ball bearings in a back to back configuration

IP67 OPTION

Resist water ingress 1m deep for up to 30 min

HEAVY DUTY INTERNAL BUMPERS

Bumpers protect the screw and nut assembly from damage at both ends of stroke

MULTIPLE SCREW TECHNOLOGIES

YOU CAN CHOOSE:

- •Bronze nuts offer smooth performance at the lowest cost
- •Ball screws offer efficiency at a cost effective price; low-backlash




Roller screws provide the highest thrust and life ratings available

Applications:

- Aligning
- Animation
- Assembly
- Automotive
- Conveyors
- Diverting Fillers
- Gating
- Material systems
- Medical equipment • Open / close
- doors Packaging
- Pick & place
- Plate positioning change
- Press fit
- Robot manipulator arms
- Sonic welding

Mounting Options:

MP2: 2 Mounting Plates BFG: Rear Flange FFG: Front Flange PCD: Rear Clevis Mount TRR: Trunnion Mount PCS: Rear Eye Mount FM2: 2 Foot Mounts



handling

- - equipment

- Sorting
- Volumetric pumps
- Web guidance
- Wire winding & more!

ROD-STYLE ELECTRIC SCREW-DRIVE ACTUATOR

RSA-HT

The RSA series of electric screw driven rod-style actuators are offered in 3 versions. The standard (ST) model comes in six sizes. The guided RSA (GSA) adds guidance and load support to the design and is available in 4 sizes. The high force (HT) model is available in 4 sizes, it incorporates torque transmission components (couplers, pulleys, belts) with higher torque capacity, high thrust bearings as well as a planetary roller screw option.

Specifications

RSA HT

RSA ST

Size	24	32	50	64
Max. Thrust (kN)	7.56	18.50	35.0	58.0
Max. Stroke (mm)	457	914	1219	1524


 Size
 24
 32
 50
 64

 Max. Thrust (lbf)
 1700
 4159
 7868
 13039

 Max. Stroke (in)
 24
 36
 48
 60

NOTE: For higher forces refer to the RSX product line.

Dimensions



SIZE: 24, 32, 50, 64

		, ,	,		
	Size	24	32	50	64
	Α	M10x1.25	M16x1.5	M20x1.5	M27x2.0
	A	↓ 25.0	J26.0	↓ 38.0	↓ 38.0
	В	51.8	65.5	94.2	116.3
	CØ	30.0	31.8	44.5	57.2
	D	10.9	12.7	17.8	17.3
SOLID	E	97.5	128.3	213.6	235.9
BALL	E	109.2	158.2	189.0	298.2
ROLLER	E	132.3	145.7	213.6	235.9

Dimensions in millimeters

	Size	24	32	50	64
	A	7/16-20	7/16-20	3/4-16	1-1/4-16
		↓ 1.00	↓ 1.13	↓ 1.50	↓ 2.50
	В	2.04	2.58	3.71	4.58
	CØ	1.18	1.25	1.75	2.25
	D	0.43	0.50	0.70	0.68
SOLID	Ε	3.84	5.05	6.44	9.29
BALL	Е	4.30	6.23	7.44	11.7
ROLLER	Е	5.21	5.74	8.41	9.29

Dimensions in inches

NOTE: YMH (Your Motor Here) will determine motor size, motor mount size and reverse parallel housing size. Complete dimensions available in RSA/GSA brochure #3600-4166; Always use solid models available at www.tolomatic.com for critical dimensions



STANDARD FEATURES
See RSA-ST Flyer (3600-4198)
for more RSA standard features



COMPANY WITH
QUALITY SYSTEM
CERTIFIED BY DNV GL
= ISO 9001 =
Certified site: Hamel, MN

USA - Headquarters Tolomatic Inc.

3800 County Road 116 Hamel, MN 55340, USA **Phone:** (763) 478-8000 Toll-Free: 1-800-328-2174 sales@tolomatic.com www.tolomatic.com

MEXICO

Centro de Servicio

Parque Tecnológico Innovación Int. 23, Lateral Estatal 431, Santiago de Querétaro, El Marqués, México, C.P. 76246 Phone: +1 (763) 478-8000 help@tolomatic.com

EUROPE Tolomatic Europe GmbH

Elisabethenstr. 20 65428 Rüsselsheim Germany

Phone: +49 6142 17604-0 help@tolomatic.eu

CHINA

Tolomatic Automation Products (Suzhou) Co. Ltd.

No. 60 Chuangye Street, Building 2 Huqiu District, SND Suzhou Jiangsu 215011 - P.R. China Phone: +86 (512) 6750-8506 TolomaticChina@tolomatic.com

All brand and product names are trademarks or registered trademarks of their respective owners. Information in this document is believed accurate at time of printing. However, Tolomatic assumes no responsibility for its use or for any errors

that may appear in this document. Tolomatic reserves the right to change the design or operation of the equipment described herein and any associated motion products without notice. Information in this document is subject to change without notice.

Visit www.tolomatic.com for the most up-to-date technical information