


FLOAT-A-SHAFT[®] Standard Series – 3:2 Ratio

Standard - High Torque - Roller Bearing




MODEL	R/LH	BORES
0231-0200	RH	3/4" X 3/4"
0232-0200	LH	3/4" X 3/4"
0233-0200	RH	3/4" X 1"
0234-0200	LH	3/4" X 1"
0235-0200	RH	3/4" X 1-1/4"
0236-0200	LH	3/4" X 1-1/4"
0237-0200	RH	1" X 1"
0238-0200	LH	1" X 1"
0239-0200	RH	1" X 1-1/4"
0240-0200	LH	1" X 1-1/4"
0241-0200	RH	1-1/4" X 1-1/4"
0242-0200	LH	1-1/4" X 1-1/4"

Need? [CLICK ON BROWSER'S BACK BUTTON TO RETURN TO PARTS SHEET.](#)

			QUANTITY											
Click on Part No. to Add to Cart			0231-0200	0232-0200	0233-0200	0234-0200	0235-0200	0236-0200	0237-0200	0238-0200	0239-0200	0240-0200	0241-0200	0242-0200
ITEM	PART NO.	DESCRIPTION												
1.	0226-9026	GEAR CASE HOUSING	1	1	1	1	1	1	1	1	1	1	1	1
2.	0200-1526	BEARING, NEEDLE, ROLLER, 1-3/8" BORE	4	4	4	4	4	4	4	4	4	4	4	4
3.	0200-1326	WASHER, THRUST, 1-3/8" BORE	4	4	4	4	4	4	4	4	4	4	4	4
4.	0200-1222	BEARING, THRUST, 1-3/8" BORE	4	4	4	4	4	4	4	4	4	4	4	4
5.	0200-3525	BUSHING, SLEEVE, STEEL, 3/4" BORE	2	2	1	1	1	1						
	0200-3526	BUSHING, SLEEVE, STEEL, 1" BORE			1	1			2	2	1	1		
	0200-3519	BUSHING, SLEEVE, STEEL, 1-1/4" BORE					1	1			1	1	2	2
6.	0200-1121	GEAR, 30 T, LH		1										
	0200-2121	GEAR, 30 T, RH	1											
	0200-1137	GEAR, 30 T, LH				1		1		1		1		1
	0200-2137	GEAR, 30 T, RH			1		1		1		1		1	
	0300-1114	GEAR, 20 T, LH		1		1		1						
	0300-2114	GEAR, 20 T, RH	1		1		1							
	0300-1113	GEAR, 20 T, LH								1		1		1
	0300-2113	GEAR, 20 T, RH							1		1		1	
7.	0200-1330	SPACER, PL, NYLON RING, .126" THICK	2	2	2	2	2	2	2	2	2	2	2	2
8.	0200-1500	KEY, STEP, 1/4" X 5/16"					1	1				1	1	2
	0200-1501	KEY, STEP, 1/4" X 7/16"			1	1			2	2	1	1		
	0200-1502	KEY, STEP, 3/16" X 1/2"	2	2	1	1	1	1						
9.	0200-1332	SPACER, PL, CELCON RING, .09" THICK	4	4	4	4	4	4	4	4	4	4	4	4
10.	0200-1812	SCREW, FILL HD, 1/4-20	6	6	6	6	6	6	6	6	6	6	6	6
11.	0100-1601	ZERK GREASE FITTING, 1/4-28	1	1	1	1	1	1	1	1	1	1	1	1
12.	0200-1225	WASHER, THRUST, 1-3/8" BORE	4	4	4	4	4	4	4	4	4	4	4	4
13.	0100-2604	SCREW, FILL HD, 1/4-28	1	1	1	1	1	1	1	1	1	1	1	1

Drawing repeated for reference



Installation


Keyway MUST extend to end of shaft. IT IS NOT POSSIBLE TO USE A SECTIONED SHAFT WITH A ROLLER BEARING FLOAT-A-SHAFT. Without removing the plastic tubes, align the Float-A-Shaft® with the shaft on which it is to be used and gently press it on. Be sure the key is properly aligned with the keyway. The plastic tubes will fall out as the shaft extends through the unit. Save the plastic tubes for removal of the Float-A-Shaft® for maintenance or repair. Be sure to reinsert the plastic tubes as the shaft is withdrawn, otherwise the internal parts will slip out of position and disassembly may be required to restore proper alignment.

Reassembly: Reference the numbering diagram on page 1 to complete the following instructions, matching the numbers with corresponding bores.

SOLID BORE REASSEMBLY: Lay Gear Case Housing (1) horizontal, with inside surface facing up. Install Roller Bearing (2) in solid bores of Gear Case Housing (1). Press from inside to outside. Inside face of roller bearing must be flush with inside machined surface of gear case housing. Next, Insert Key (8) into slot of Sleeve Bushing (5) and insert the plastic tube to hold it in place. Install Gear (6) over the Sleeve Bushing (5) positioning it over Key (8). Install Plastic Spacer (9) on both sides of gear. Lubricate Roller Bearing (2), Thrust Bearing (4), and Gear (7) manually (See "Lubrication"). Install a Thrust Washer (3), Thrust Bearing (4), and Thrust Washer (3) on each side of gear. Lay the Gear Case Housing (1) horizontal, with the solid bore vertical and inside surface facing up. Install gear, sleeve and bearing assembly into the solid bore.

SPLIT BORE REASSEMBLY: Insert Key (8) into slot of Sleeve Bushing (5) and insert the plastic tube to hold it in place. Install

Shaft Keyway Types



Gear (6) over the Sleeve Bushing (5) positioning it over Key (8). Install Plastic Spacer (9) and a Nylon Ring Spacer (7) on both sides of gear. Lubricate all bearings and the Gear (6) manually (See "Lubrication"). Install a Thrust Washer (12), Thrust Bearing (4), and Thrust Washer (12) on each side of gear. Install a Roller Bearing (2) on each side of Gear (6). Lay the completed assembly into the split bore of the Gear Case Housing (1), making sure the teeth of the gears mesh.

CAUTION: When trying to get the gears to mesh, rotate the gears to prevent possible damage to the teeth. Next, cover gears and bearings with approximately 3 oz. of lubricant. To complete assembly, install the other half of the Gear Case Housing (1) and tighten the Screws (10) in the order shown here. In case of shaft binding, check for possible

misalignment of the shafts or for oversized shaft diameters.

Shaft Requirements: Shafts should be made of power transmission steel grade 4140 or better. A tolerance of $\pm .000/- .002$ is recommended for the shaft diameters. The shaft surfaces should be 32 RMS maximum for stationary applications, and 16 RMS maximum for traversing applications. Shaft straightness should be .0015 TIR per foot.

LUBRICATION AND MAINTENANCE SCHEDULE: All Float-A-Shaft® gear boxes have been lubricated at the factory with Mobilith® SHC 460. Standard Float-A-Shaft® gear boxes are initially filled with 2.8 oz. (82.8 ml) of grease to achieve 54% fill on the units. However, units require more lubrication prior to operation. Periodic re-lubrication is also necessary for optimum performance. When re-lubricating, inject Mobilith® SHC 460 (maximum operating temperature of 300°F or higher and EP rated) into gear case, as required, via the grease zerk provided.

Mobilith® SHC 460 - 14 oz grease cartridge • P/N 0100-1605
Lubrication and maintenance schedules are dependent on the application. General guidance is provided below and a maintenance plan can be developed based on the use case.

MAINTENANCE	USE CASE		
	Continuous/ Heavy Duty	Intermittent/ Light Duty	Minimal
Inject 1/4 oz. of Mobilith SHC460 into gear housing	1 ½ Months	3 Months	6 Months
Disassemble and purge unit. Hand lubricate all bearings and gears with 3 oz. of Mobilith SHC460	6 Months	1 Year	1 Year

Mobilith® SHC 460 is a registered trademark of Exxon Mobil Corporation, www.mobil.com
Float-A-Shaft® is a registered trademark of Tolomatic, Inc.

Tolomatic
EXCELLENCE IN MOTION

3800 County Road 116, Hamel, MN 55340 USA
<https://www.Tolomatic.com> • Email: Help@Tolomatic.com
Phone: (763) 478-8000 • Toll Free: 1-800-328-2174

COMPANY WITH
QUALITY SYSTEM
CERTIFIED BY DNV
= ISO 9001 =

All brand and product names are trademarks or registered trademarks of their respective owners. Information in this document is believed accurate at time of printing. However, Tolomatic assumes no responsibility for its use or for any errors that may appear in this document. Tolomatic reserves the right to change the design or operation of the equipment described herein and any associated motion products without notice. Information in this document is subject to change without notice.

Visit www.tolomatic.com for the most up-to-date technical information