


SMALL GEARBOXES

We have expanded our proven Slide-Rite gearbox line with the smallest size featuring a smaller bore and smaller footprint. There are thousands of uses for this versatile gearbox.

SGB



SEALED BEARINGS


ANODIZED ALUMINUM HOUSING
• For lightweight strength

HARDENED GEARS
Hardened 4140 steel for long life

LUBED FOR LIFE
Pre-lubricated with
Magnalube-G grade grease

A	B	C	
1.436	1.448	1.826	in
36.47	36.78	46.38	mm

ROTATION CHOICE



Contact Tolomatic: If interested in stainless steel construction or embedded shafts



Applications:

- Conveying
- Medical Equipment
- Cosmetics
- Packaging
- Labeling
- Pharmaceutical
- Life Science
- Printing
- Material Handling
- and More

SMALL GEARBOXES

SPECIFICATIONS

SGB05, 1:1, $\frac{1}{4} \times \frac{1}{4}$		
1/2-inch (12.7mm) Bore-to-Bore Centerline		
RPM	OUTPUT - TORQUE	
	(lb-in)	(N-m)
50	12	1.36
100	11	1.24
200	11	1.24
600	10	1.13
900	9	1.02
1200	8	0.90
1800	7	0.79
INPUT TORQUE = OUTPUT TORQUE / .6		
MAX HAND TORQUE < 25 RPM = 33 LB-IN		

SGB07, 1:1, $\frac{3}{8} \times \frac{3}{8}$		
3/4-inch (19.05mm) Bore-to-Bore Centerline		
RPM	OUTPUT - TORQUE	
	(lb-in)	(N-m)
50	20	2.26
100	19	2.15
200	18	2.03
600	14	1.58
900	13	1.47
1200	12	1.36
1800	10	1.13
INPUT TORQUE = OUTPUT TORQUE / .6		
MAX HAND TORQUE < 25 RPM = 56 LB-IN		


SGB



COMPLETE INFORMATION, SIZING ASSISTANCE AND SOLID MODELS AVAILABLE: CONTACT TOLOMATIC

tolomatic.com/ask

Dimensions



	SGB05		SGB07	
	in	mm	in	mm
A	1.436	36.47	1.448	36.78
B	.718	18.24	.724	18.29
C	.468	11.89	.538	13.67
D	Ø.250	Ø 6.35	Ø.375	Ø 9.53
E	10-32 UNF-2B	10-32 UNF-2B	10-32 UNF-2B	10-32 UNF-2B
F	3/32	2.36	3/32	2.36
G	.500 C.D.	12.7 C.D.	.750 C.D.	19.05 C.D.
H	.468	11.89	.538	13.67
J	1.436	36.47	1.826	46.38
K	1.060	26.92	1.072	27.23
L	.530	13.46	.536	13.61
M	.280	7.11	.350	8.89
N	1.120	28.45	1.476	37.49
P	6-32 UNC-2B X .313	6-32 UNC-2B X 7.95	6-32 UNC-2B X .313	6-32 UNC-2B X 7.95
R	6-32 UNC-2B X .313	6-32 UNC-2B X 7.95	6-32 UNC-2B X .313	6-32 UNC-2B X 7.95
S	1.014	25.76	1.058	26.87
T	.794	20.17	1.058	26.87



MADE IN U.S.A.

TolomaticTM
EXCELLENCE IN MOTION

COMPANY WITH
QUALITY SYSTEM
CERTIFIED BY DNV
= ISO 9001 =
Certified site: Hamel, MN

USA - Headquarters

Tolomatic Inc.
3800 County Road 116
Hamel, MN 55340, USA
Phone: (763) 478-8000
Toll-Free: **1-800-328-2174**
sales@tolomatic.com
www.tolomatic.com

MEXICO

Centro de Servicio
Parque Tecnológico Innovación
Int. 23, Lateral Estatal 431,
Santiago de Querétaro,
El Marqués, México, C.P. 76246
Phone: +1 (763) 478-8000
help@tolomatic.com

EUROPE

Tolomatic Europe GmbH
Elisabethenstr. 20
65428 Rüsselsheim
Germany
Phone: +49 6142 17604-0
help@tolomatic.eu
www.tolomatic.com/de-de

CHINA

Tolomatic Automation Products (Suzhou) Co. Ltd.
No. 60 Chuangye Street, Building 2
Huqiu District, SND Suzhou
Jiangsu 215011 - P.R. China
Phone: +86 (512) 6750-8506
Tolomatic_China@tolomatic.com

All brand and product names are trademarks or registered trademarks of their respective owners. Information in this document is believed accurate at time of printing. However, Tolomatic assumes no responsibility for its use or for any errors

that may appear in this document. Tolomatic reserves the right to change the design or operation of the equipment described herein and any associated motion products without notice. Information in this document is subject to change without notice.

Visit www.tolomatic.com for the most up-to-date technical information